


THMWJ-16-1U-P-1 Cut Sheet



TE Wire & Cable Type J thermocouple extension wire, unshielded, 2 conductors, 16 AWG, iron and copper-nickel, PVC conductor insulation material, white and red, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWJ-16-1U-P-1>

Technical Specifications

| | |
|--------------------------------------|------------------------|
| Brand | TE Wire & Cable |
| Item | Wire |
| Sensor Type | Type J thermocouple |
| Wire/Cable Type | Extension |
| Application | Temperature |
| Flexibility | Semi-flexible |
| Conductors | 2 conductors |
| Conductor Size | 16 AWG |
| Conductor Stranding | Solid |
| Conductor Material | Iron and copper-nickel |
| Conductor Insulation Material | PVC |

| | |
|---------------------------------------|---|
| Conductor Insulation Color | White and red |
| Shielding | Unshielded |
| Jacket Material | PVC |
| Jacket Color | Black |
| Nominal Overall Cable Diameter | 0.188in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 50 to 99ft = Coil• 100 to 1000ft = 14 x 7in Reel |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | none |
| UL Recognized File # | none |
| UL Hazardous File # | none |
| CSA File # | none |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |