

THMWJ-20-1S-P-1 Cut Sheet

TE Wire & Cable Type J thermocouple extension wire, shielded, 2 conductors, 20 AWG, iron and copper-nickel, PVC conductor insulation material, white and red, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWJ-20-1S-P-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Wire
Sensor Type	Type J thermocouple
Wire/Cable Type	Extension
Application	Temperature
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	2 conductors
Conductor Size	20 AWG
Conductor Stranding	Solid
Conductor Material	Iron and copper-nickel
Conductor Insulation Material	PVC

Conductor Insulation Color	White and red
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.214in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 50 to 99ft = Coil• 100 to 850ft = 14 x 7in Reel• 851 to 1215ft = 14 x 10in Reel• 1216 to 1865ft = 16 x 10in Reel• 1866 to 2605ft = 18 x 10in Reel• 2606 to 3390ft = 18 x 13in Reel• 3391 to 5000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement