


THMWJ-20-1S-P-1 Cut Sheet

TE Wire & Cable Type J thermocouple extension wire, shielded, 2 conductors, 20 AWG, iron and copper-nickel, PVC conductor insulation material, white and red, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWJ-20-1S-P-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Wire
Sensor Type	Type J thermocouple
Wire/Cable Type	Extension
Application	Temperature
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	2 conductors
Conductor Size	20 AWG
Conductor Stranding	Solid
Conductor Material	Iron and copper-nickel
Conductor Insulation Material	PVC

Conductor Insulation Color	White and red
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.214in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 1 to 100ft = Coil• 101 to 808ft = 14 x 7in Reel• 809 to 1154ft = 14 x 10in Reel• 1155 to 1787ft = 16 x 10in Reel• 1788 to 2516ft = 18 x 10in Reel• 2517 to 3271ft = 18 x 13in Reel• 3272 to 7026ft = 24 x 17in Wooden Reel• 7027 to 11552ft = 30 x 17in Wooden Reel• 11553 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	RoHS Statement