


THMWJ-20-2S-P-1 Cut Sheet

TE Wire & Cable Type J thermocouple PLTC and ITC extension cable, shielded, 2 twisted pairs, 20 AWG, iron and copper-nickel, PVC conductor insulation material, white and red, PVC jacket, black, cut to length.



For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWJ-20-2S-P-1>

Technical Specifications

| | |
|--------------------------------------|------------------------|
| Brand | TE Wire & Cable |
| Item | Cable |
| Sensor Type | Type J thermocouple |
| Wire/Cable Type | Extension |
| UL Wire/Cable Type | PLTC and ITC |
| Application | Temperature |
| Flexibility | Semi-flexible |
| Voltage Rating | 300V |
| Conductors | 2 twisted pairs |
| Conductor Size | 20 AWG |
| Conductor Stranding | Solid |
| Conductor Material | Iron and copper-nickel |
| Conductor Insulation Material | PVC |

| | |
|---------------------------------------|--|
| Conductor Insulation Color | White and red |
| Shielding | Shielded |
| Jacket Material | PVC |
| Jacket Color | Black |
| Nominal Overall Cable Diameter | 0.331in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 25 to 75ft = Coil• 76 to 355ft = 14 x 7in Reel• 356 to 510ft = 14 x 10in Reel• 511 to 780ft = 16 x 10in Reel• 781 to 1090ft = 18 x 10in Reel• 1091 to 1415ft = 18 x 13in Reel• 1416 to 3170ft = 24 x 17in Wooden Reel• 3171 to 5000ft = 30 x 17in Wooden Reel |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E54438 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |