


# THMWJ-20-4S-P-1 Cut Sheet

TE Wire & Cable Type J thermocouple PLTC and ITC extension cable, shielded, 4 twisted pairs, 20 AWG, iron and copper-nickel, PVC conductor insulation material, white and red, PVC jacket, black, cut to length.



For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWJ-20-4S-P-1>

## Technical Specifications

<b>Brand</b>	TE Wire & Cable
<b>Item</b>	Cable
<b>Sensor Type</b>	Type J thermocouple
<b>Wire/Cable Type</b>	Extension
<b>UL Wire/Cable Type</b>	PLTC and ITC
<b>Application</b>	Temperature
<b>Flexibility</b>	Semi-flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	4 twisted pairs
<b>Conductor Size</b>	20 AWG
<b>Conductor Stranding</b>	Solid
<b>Conductor Material</b>	Iron and copper-nickel
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	White and red

<b>Shielding</b>	Shielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.377in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 25 to 75ft = Coil</li><li>• 76 to 275ft = 14 x 7in Reel</li><li>• 276 to 390ft = 14 x 10in Reel</li><li>• 391 to 600ft = 16 x 10in Reel</li><li>• 601 to 840ft = 18 x 10in Reel</li><li>• 841 to 1090ft = 18 x 13in Reel</li><li>• 1091 to 2445ft = 24 x 17in Wooden Reel</li><li>• 2446 to 3910ft = 30 x 17in Wooden Reel</li><li>• 3911 to 5000ft = Large Wooden Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E54438
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>