


# THMWK-20-1U-F-1 Cut Sheet



TE Wire & Cable Type K thermocouple extension wire, unshielded, 2 conductors, 20 AWG, nickel-chromium and nickel-aluminum, FEP Teflon conductor insulation material, yellow and red, FEP Teflon jacket, brown, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWK-20-1U-F-1>

## Technical Specifications

<b>Brand</b>	TE Wire & Cable
<b>Item</b>	Wire
<b>Sensor Type</b>	Type K thermocouple
<b>Wire/Cable Type</b>	Extension
<b>Application</b>	Temperature
<b>Flexibility</b>	Semi-flexible
<b>Conductors</b>	2 conductors
<b>Conductor Size</b>	20 AWG
<b>Conductor Stranding</b>	Solid
<b>Conductor Material</b>	Nickel-chromium and nickel-aluminum
<b>Conductor Insulation Material</b>	FEP Teflon

<b>Conductor Insulation Color</b>	Yellow and red
<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	FEP Teflon
<b>Jacket Color</b>	Brown
<b>Nominal Overall Cable Diameter</b>	0.116in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 50 to 99ft = Coil</li><li>• 100 to 1000ft = 14 x 7in Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	none
<b>UL Recognized File #</b>	none
<b>UL Hazardous File #</b>	none
<b>CSA File #</b>	none
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>