

THMWK-20-1U-HG-1 Cut Sheet



TE Wire & Cable Type K thermocouple extension wire, unshielded, 2 conductors, 20 AWG, nickel-chromium and nickel-aluminum, high temperature fiberglass conductor insulation material, yellow and red, high temperature fiberglass jacket, brown, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWK-20-1U-HG-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Wire
Sensor Type	Type K thermocouple
Wire/Cable Type	Extension
Application	Temperature
Flexibility	Semi-flexible
Conductors	2 conductors
Conductor Size	20 AWG
Conductor Stranding	Solid
Conductor Material	Nickel-chromium and nickel-aluminum
Conductor Insulation Material	High temperature fiberglass
Conductor Insulation Color	Yellow and red
Shielding	Unshielded
Jacket Material	High temperature fiberglass
Jacket Color	Brown
Nominal Overall Cable Diameter	0.142in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 1 to 99ft = Coil• 100 to 1935ft = 14 x 7in Reel• 1936 to 2765ft = 14 x 10in Reel• 2766 to 4235ft = 16 x 10in Reel• 4236 to 5000ft = 18 x 10in Reel

Agency Approvals

UL Listed File #	none
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	none
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement