

THMWT-20-1S-P-1 Cut Sheet

TE Wire & Cable Type T thermocouple extension wire, shielded, 2 conductors, 20 AWG, copper and copper-nickel, PVC conductor insulation material, blue and red, PVC jacket, blue, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/THMWT-20-1S-P-1>

Technical Specifications

Brand	TE Wire & Cable	Shielding	Shielded
Item	Wire	Jacket Material	PVC
Sensor Type	Type T thermocouple	Jacket Color	Blue
Wire/Cable Type	Extension	Nominal Overall Cable Diameter	0.214in
Application	Temperature	Bulk Length	Cut to length
Flexibility	Semi-flexible	Package Type	1 to 100ft = Coil, 101 to 808ft = 14 x 7in Reel, 809 to 1154ft = 14 x 10in Reel, 1155 to 1787ft = 16 x 10in Reel, 1788 to 2516ft = 18 x 10in Reel, 2517 to 3271ft = 18 x 13in Reel, 3272 to 7026ft = 24 x 17in Wooden Reel, 7027 to 11552ft = 30 x 17in Wooden Reel, 11553 to MAX = Large Wooden Reel
Voltage Rating	300V		
Conductors	2 conductors		
Conductor Size	20 AWG		
Conductor Stranding	Solid		
Conductor Material	Copper and copper-nickel		
Conductor Insulation Material	PVC		
Conductor Insulation Color	Blue and red		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	RoHS Statement