

# TJN40 Cut Sheet



Edison fuse, TJN series, Class T, current-limiting, extremely fast-acting, 40A, 300 VAC, ferrule. Package of 10. Feeder/branch, semiconductor protection applications.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TJN40>

## Technical Specifications

|                              |  |
|------------------------------|--|
| <b>Brand</b>                 | Edison   |
| <b>Item</b>                  | Fuse   |
| <b>Series</b>                | TJN  |
| <b>Fuse Class</b>            | Class T  |
| <b>Current-Limiting</b>      | Yes  |
| <b>Curve Characteristics</b> | Extremely fast-acting                                |
| <b>Amperage Rating</b>       | 40A  |
| <b>Voltage Rating</b>        | 300 VAC  |
| <b>Body Type</b>             | Ferrule  |
| <b>Size</b>                  | 0.56x0.88in or 14.2x22.3mm                           |
| <b>Quantity per Pack</b>     | 10   |
| <b>Application</b>           | Feeder/branch, semiconductor protection applications |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E162363                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 53787                                  |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |
| <b>Other</b>                | None                                   |