


TK26E-P64 Cut Sheet



Fuji Electric TK26E series thermal overload relay, 0.64-0.96A adjustable, bi-metallic, direct mount power connection(s). For use with SC-E02x, SC-E03x, SC-E04x and SC-E05x contactors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TK26E-P64>

Technical Specifications

Brand	Fuji Electric
Item	Relay
Series	TK26E
Relay Type	Thermal overload
Full Load Amperage Range	0.64-0.96A adjustable
Operation Type	Bi-metallic
Auxiliary Contacts	(1) N.O./ (1) N.C.
Trip Class	Trip Class 10A
Phase Loss Sensitive	Yes
Connection	Direct mount power
For Use With	SC-E02x, SC-E03x, SC-E04x and SC-E05x contactors

Agency Approvals

UL Listed File #	E44592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document