

TKHM-Z/TSM-Z/T4 Cut Sheet

di-soric patch cable signal converter, 4-pin M8 axial female to 4-pin M8 axial male, pulse stretcher, 10–35 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TKHM-Z/TSM-Z/T4>



Technical Specifications

Brand	di-soric
Item	Signal converter
Form Factor	Patch cable
Connector Type	4-pin M8 axial female to 4-pin M8 axial male
Function	Pulse stretcher
Operating Voltage	10–35 VDC
Operating Temperature	-20 to +70 °C
Material	Plastic
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/TKHM-Z_TSM-Z_T4.pdf
See store item page for other formats.