

TL46-WJ-815 Cut Sheet



Datalogic contrast sensor, rectangular, diffuse, RGB, vertical spot orientation, 6-12mm sensing distance, selectable light-on/dark-on, PNP, teach-in button, 50 kHz switching frequency, aluminum housing, 5-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TL46-WJ-815>

Technical Specifications

Brand	Datalogic	Switching Output	PNP
Item	Contrast sensor	Sensing Distance	6-12mm
Shape	Rectangular	Sensitivity	Teach-in button
Housing Size	81.5 x 31.9 x 60.7mm	Operation Mode	Selectable light-on/dark-on
IP Rating	IP67	Switching Frequency	50 kHz
Housing Material	Aluminum	Light Emission (NP)	RGB
Sensing Method	Diffuse	Spot Orientation	Vertical
Sensor Type	Print mark	Connection	5-pin M12 quick-disconnect
Operating Voltage	10-30 VDC	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E227487
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TL46-WJ-815.pdf>
See store item page for other formats.