

TRD-MX360VD Cut Sheet



Koyo TRD-MX series incremental (quadrature) rotary encoder, light duty, 5 VDC, axial exit, line driver (differential) output, 360 ppr, 4mm solid shaft, 1in diameter body, IP50, 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TRD-MX360VD>

Technical Specifications

Brand	Koyo
Item	Encoder
Series	TRD-MX
Feedback Type	Incremental (quadrature)
Encoder Type	Rotary
Duty Rating	Light duty
Voltage Rating	5 VDC
Exit Orientation	Axial
Encoder Output Type	Line driver (differential)
Encoder Resolution	360 ppr
Shaft Type	Solid
Shaft Diameter	4mm
Radial Shaft Load	10N

Axial Shaft Load	5N
Frequency Response	100 kHz
Speed Rating	6000rpm
Flange Mount	No
Encoder Body Diameter	1in
Housing Material	Aluminum
IP Rating	IP50
Cable Length	6.5ft/2m
Cable Diameter Size	5mm
Wire Size	26 AWG
Connector Type	Pigtail
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E189395
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TRD-MX360VD.pdf>
See store item page for other formats.