

TRD-NH4-RZVWD Cut Sheet



Koyo TRD-N series incremental (quadrature) rotary encoder, medium duty, 5 VDC, radial exit, line driver (differential) output, 4 ppr, 8mm hollow shaft, 50mm diameter body, IP65, 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TRD-NH4-RZVWD>

Technical Specifications

Brand	Koyo
Item	Encoder
Series	TRD-N
Feedback Type	Incremental (quadrature)
Encoder Type	Rotary
Duty Rating	Medium duty
Voltage Rating	5 VDC
Exit Orientation	Radial
Encoder Output Type	Line driver (differential)
Encoder Resolution	4 ppr
Shaft Type	Hollow
Shaft Diameter	8mm
Radial Shaft Load	50N
Axial Shaft Load	30N
Frequency Response	100 kHz
Speed Rating	3000rpm
Flange Mount	No
Encoder Body Diameter	50mm
Housing Material	Aluminum
IP Rating	IP65
Cable Length	6.5ft/2m
Cable Diameter Size	6.4mm
Wire Size	24 AWG
Connector Type	Pigtail

Agency Approvals

UL Listed File #	E189395
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document