

# TRD-SHR500VW0D Cut Sheet



Koyo TRD-SR series incremental (quadrature) rotary encoder, light duty, 5 VDC, radial exit, line driver (differential) output, 500 ppr, 8mm hollow shaft, 40mm diameter body, IP65, 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TRD-SHR500VW0D>

## Technical Specifications

<b>Brand</b>	Koyo	<b>Radial Shaft Load</b>	30N
<b>Item</b>	Encoder	<b>Axial Shaft Load</b>	20N
<b>Series</b>	TRD-SR	<b>Frequency Response</b>	200 kHz
<b>Feedback Type</b>	Incremental (quadrature)	<b>Speed Rating</b>	6000rpm
<b>Encoder Type</b>	Rotary	<b>Flange Mount</b>	No
<b>Duty Rating</b>	Light duty	<b>Encoder Body Diameter</b>	40mm
<b>Voltage Rating</b>	5 VDC	<b>Housing Material</b>	Aluminum
<b>Exit Orientation</b>	Radial	<b>IP Rating</b>	IP65
<b>Encoder Output Type</b>	Line driver (differential)	<b>Cable Length</b>	6.5ft/2m
<b>Encoder Resolution</b>	500 ppr	<b>Cable Diameter Size</b>	6mm
<b>Shaft Type</b>	Hollow	<b>Wire Size</b>	26 AWG
<b>Shaft Diameter</b>	8mm	<b>Connector Type</b>	Pigtail

## Agency Approvals

<b>UL Listed File #</b>	E189395
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/TRD-SHR500VW0D.pdf>  
See store item page for other formats.