

TRD-SR360VWD Cut Sheet



JTEKT TRD-SR series incremental (quadrature) rotary encoder, 5 VDC, line driver (differential) output, light duty, 360 ppr, 6mm solid shaft, 40mm diameter body, IP65, 6.5ft/2m cable length, radial exit, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TRD-SR360VWD>

Technical Specifications

Brand	JTEKT
Item	Encoder
Series	TRD-SR
Feedback Type	Incremental (quadrature)
Encoder Type	Rotary
Voltage Rating	5 VDC
Encoder Output Type	Line driver (differential)
Duty Rating	Light duty
Programmable Encoder Resolution	No
Encoder Resolution	360 ppr
Shaft Type	Solid
Shaft Diameter	6mm
Radial Shaft Load	30N

Axial Shaft Load	20N
Frequency Response	200 kHz
Speed Rating	6000rpm
Flange Mount	No
Encoder Body Diameter	40mm
Housing Material	Aluminum
IP Rating	IP65
Cable Length	6.5ft/2m
Cable Diameter Size	6mm
Wire Size	26 AWG
Exit Orientation	Radial
Connector Type	Pigtail
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E189395
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/TRD-SR360VWD.pdf>
See store item page for other formats.