

# TRM-10-D-24AD Cut Sheet



ProSense multi-mode relay timer, 0.05 seconds to 999 hours selectable timing range, 24 VAC/VDC operating voltage, 10A contact rating, (1) DPDT timed relay output(s), socket mount, 11-pin. Requires Macromatic 70170-D relay socket.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TRM-10-D-24AD>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Relay timer
<b>Timer Type</b>	Multi-mode
<b>Indicator</b>	LED
<b>Timing Range</b>	0.05 seconds to 999 hours selectable
<b>Operating Voltage</b>	24 VAC/VDC
<b>Timer Output Type(s)</b>	(1) DPDT timed relay
<b>Timer Function(s)</b>	<ul style="list-style-type: none"><li>• on-delay</li><li>• triggered on-delay</li><li>• off-delay</li><li>• on/off delay</li><li>• interval</li><li>• single-shot</li><li>• falling edge (single-shot)</li><li>• on-flasher</li><li>• off-flasher</li><li>• watchdog</li></ul>
<b>Contact Rating</b>	10A
<b>Mounting</b>	Socket
<b>Connector Type</b>	11-pin
<b>Requires</b>	Macromatic 70170-D relay socket

## Agency Approvals

<b>UL Listed File #</b>	E191059
<b>UL Recognized File #</b>	E191059
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	602618
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>