

TSDA25N-AP-0284-H Cut Sheet



ProSense temperature switch, integral Pt1000 RTD, -13 to 284 deg F, 50mm insertion length, 6mm probe diameter, 1/4in male NPT process connection, Output: switch PNP, N.O., Output 2: switch PNP, N.O.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TSDA25N-AP-0284-H>

Technical Specifications

Brand	ProSense
Item	Temperature switch
Sensor Type	Integral Pt1000 RTD
Temperature Sensing Range	-13 to 284 deg F
Setpoint Range	-4 to 284 deg F
Insertion Length	50mm
Probe Diameter	6mm
Process Connection	1/4in male NPT
Output	Switch PNP, N.O.
Output 2	Switch PNP, N.O.
Operating Voltage	9.6 to 32 VDC
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Cable purchased separately

Agency Approvals

UL Listed File #	E324411
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document