

TTD-20-N40300F-H Cut Sheet



ProSense temperature transmitter, isolated, Pt100 RTD input, -40 to 300 deg F fixed, 4-20 mA output, 20 to 32 VDC operating voltage, M12 in-line mount, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TTD-20-N40300F-H>

Technical Specifications

Brand	ProSense
Item	Temperature transmitter
Isolation	Isolated
Field Configurable	No
Input RTD Signal Types	Pt100 RTD
Factory Calibrated Temperature Range	-40 to 300 deg F fixed
Output Current Signal Range	4-20 mA
Operating Voltage	20 to 32 VDC
Housing Material	Plastic
Mounting	M12 in-line
Electrical Connection	4-pin M12 quick-disconnect

Agency Approvals

UL Listed File #	E324411
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document