

TTD25N-20-0300F-H Cut Sheet



ProSense temperature transmitter, integral Pt1000 RTD, 0 to 300 deg F, 50mm insertion length, 8.3mm probe diameter, 1/4in male NPT process connection, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TTD25N-20-0300F-H>

Technical Specifications

| | |
|---------------------------|----------------------------|
| Brand | ProSense |
| Item | Temperature transmitter |
| Sensor Type | Integral Pt1000 RTD |
| Temperature Sensing Range | 0 to 300 deg F |
| Probe Diameter | 8.3mm |
| Insertion Length | 50mm |
| Process Connection | 1/4in male NPT |
| Analog Output | 4-20 mA |
| Operating Voltage | 10-30 VDC |
| Electrical Connection | 4-pin M12 quick-disconnect |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E324411 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TTD25N-20-0300F-H.pdf>
See store item page for other formats.