

TU1-C1-0E Cut Sheet



Micro Detectors ultrasonic proximity sensor, tubular, 30mm diameter x 124mm body, polybutylene terephthalate housing, 0-10 VDC analog output, 300-2500mm sensing distance, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TU1-C1-0E>

Technical Specifications

Brand	Micro Detectors	Number of Wires	4
Item	Proximity sensor	Analog Output	0-10 VDC
Sensor Type	Ultrasonic	Sensing Distance	300-2500mm
Shape	Tubular	Operating Voltage	19-30 VDC
Housing Size	30mm diameter x 124mm body	IP Rating	IP67
Housing Material	Polybutylene terephthalate	Connection	4-pin M12 quick-disconnect
Barrel Type	Threaded	Includes	Mounting hardware
Sensing Method	Diffuse	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E187310
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document