

TVK35-025-4X-120A Cut Sheet



Stratus vortex cooler kit, 2500 BTUH (732W), 35 SCFM (991 SLPM), 120 VAC operating voltage, stainless steel body. For use with NEMA 4, NEMA 4X and NEMA 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TVK35-025-4X-120A>

Technical Specifications

Brand	Stratus
Item	Vortex cooler kit
Cooling Capacity	2500 BTUH (732W)
Flow Rating	35 SCFM (991 SLPM)
Operating Voltage	120 VAC
Body Material	Stainless steel
For Use With	NEMA 4, NEMA 4X and NEMA 12 enclosures
Kit Includes	(1) Stratus TV35-025-4X vortex cooler, (1) NITRA AFR2-3233 pneumatic filter regulator, (1) NITRA AFE2-31 filter element, (1) Stego 011169-00 adjustable thermostat and (1) NITRA DVD-2BC2A-120A solenoid valve

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document