

# TVK35-025-4X-24D Cut Sheet



Stratus vortex cooler kit, 2500 BTUH (732W), 35 SCFM (991 SLPM), 24 VDC operating voltage, stainless steel body. For use with NEMA 4, NEMA 4X and NEMA 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TVK35-025-4X-24D>

## Technical Specifications

<b>Brand</b>	Stratus
<b>Item</b>	Vortex cooler kit
<b>Cooling Capacity</b>	2500 BTUH (732W)
<b>Flow Rating</b>	35 SCFM (991 SLPM)
<b>Operating Voltage</b>	24 VDC
<b>Body Material</b>	Stainless steel
<b>For Use With</b>	NEMA 4, NEMA 4X and NEMA 12 enclosures
<b>Kit Includes</b>	(1) Stratus TV35-025-4X vortex cooler, (1) NITRA AFR2-3233 pneumatic filter regulator, (1) NITRA AFE2-31 filter element, (1) Stego 011169-00 adjustable thermostat and (1) NITRA DVD-2BC2A-24D solenoid valve

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>