

# TW-DB-SET-28R Cut Sheet



Wera Bit-Check standard driver bit set, Phillips, Torx, tamperproof torx, external hex, slotted and square, 31 pieces, 1in bit length, 1/4in drive, imperial.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TW-DB-SET-28R>

## Technical Specifications

Brand	Wera	Ratcheting	Yes
Series	Bit-Check	Directional Change	Switch lever
Item	Driver bit set	Return Angle	6 degrees
Number of Pieces	31	Lock Mechanism	Ballpoint socket, retaining ring bit holder and Rapidaptor quick-release bit holder
Bit Type	Standard	Set Includes	Ratchet, 1/4in Rapidaptor universal bit holder, 1/4in socket drive adapter, 5.5mm slotted bit, (6) Phillips bits (#3, (2) #1, (3) #2), (5) Hex-Plus bits (3/32, 1/8, 5/32, 3/16, 1/4in), (5) Square bits (#1, #3, (3) #2), (6) Torx bits (T10, T15, T20, T25, T30, T40), (5) Tamper-proof Torx bits (T10, T15, T20, T25, T30), plastic case
Measurement Type	Imperial		
Insulated	No	Application	Bit holding, screwdriving and ratcheting
Drive Size	1/4in		
Bit Length	1in		
Tip Type	Phillips, Torx, tamperproof torx, external hex, slotted and square		

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>