

TW-DB-SET-28R Cut Sheet



Wera Bit-Check standard driver bit set, 31 pieces, 1in bit length, 1/4in drive, imperial.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TW-DB-SET-28R>

Technical Specifications

Brand	Wera
Series	Bit-Check
Item	Driver bit set
Number of Pieces	31
Bit Type	Standard
Measurement Type	Imperial
Insulated	No
Drive Size	1/4in
Bit Length	1in
Tip Type	Phillips, Torx, tamperproof torx, hex, slotted and square
Ratcheting	Yes
Directional Change	Switch lever
Return Angle	6 degrees
Lock Mechanism	Secure socket ball lock mechanism
Set Includes	Ratchet, 1/4in Rapidaptor universal bit holder, 1/4in socket drive adapter, 5.5mm slotted bit, (6) Phillips bits (#3, (2) #1, (3) #2), (5) Hex-Plus bits (3/32, 1/8, 5/32, 3/16, 1/4in), (5) Square bits (#1, #3, (3) #2), (6) Torx bits (T10, T15, T20, T25, T30, T40), (5) Tamper-proof Torx bits (T10, T15, T20, T25, T30), plastic case
Application	Bit holding, screwdriving and ratcheting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document