

TW-TD-11-29 Cut Sheet



Wera Kraftform 7400 screwdriver, 11-29 in-lb set point, +/-6% (DIN EN ISO 6789) accuracy, numerical torque value, audible excess load signal, 1/4in drive.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TW-TD-11-29>

Technical Specifications

Brand	Wera
Series	Kraftform 7400
Item	Screwdriver
Screwdriver Type	Adjustable torque
Setpoint Range	11-29 in-lb
Accuracy	+/-6% (DIN EN ISO 6789)
Scale	Numerical torque value
Indicator	Audible excess load signal

Drive Size	1/4in
Lock Mechanism	Rapidaptor quick-release bit holder
Handle Type	Kraftform ergonomic handle
Screwdriver Features	1/4in Rapidaptor universal bit holder
Insulated	No
Ratcheting	No
Overall Length	6.1in (155mm)
Application	Screwdriving and torque driving

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document