

TW242410HWT Cut Sheet



AttaBox Triton series enclosure, NEMA 1/3/3R/4X/12, 24 x 24 x 10in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (4) twist-lock latches, padlock hasp and staple, SAR acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TW242410HWT>

Technical Specifications

Brand	AttaBox
Item	Enclosure
Series	Triton
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/3/3R/4X/12
IP Rating	IP66
Nominal Enclosure Height	24in
Nominal Enclosure Width	24in
Nominal Enclosure Depth	10in
Mounting	Wall
Integral Mounting Feet	Yes
Integral Mounting Flange	No

Dual Access	No
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	(4) twist-lock latches
Padlock Attachment Type	Padlock hasp and staple
Window Material	SAR acrylic
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	E333478
UL Hazardous File #	none
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/TW242410HWT.pdf>
See store item page for other formats.