

# TY-10 Cut Sheet



Iboco braided expandable sleeving, 0.37in nominal inside diameter, 0.31-0.86in stretching range, black, 325ft coil.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TY-10>

---

## Technical Specifications

<b>Brand</b>	Iboco
<b>Item</b>	Braided expandable sleeving
<b>Nominal Inside Diameter</b>	0.37in
<b>Stretching Range</b>	0.31-0.86in
<b>Color</b>	Black
<b>Coil Length</b>	325ft

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>