

TY-20 Cut Sheet



Iboco braided expandable sleeving, 0.75in nominal inside diameter, 0.63-1.37in stretching range, black, 164ft coil.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TY-20>

Technical Specifications

Brand	Iboco
Item	Braided expandable sleeving
Nominal Inside Diameter	0.75in
Stretching Range	0.63-1.37in
Color	Black
Coil Length	164ft

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document