

TY27MX Cut Sheet



ABB - Thomas & Betts Ty-Rap series steel tooth cable tie, UV resistant, nylon 6.6, 13.4in length, 0.28in width, 120 lb tensile strength, 4in maximum bundle diameter, black. Package of 500.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TY27MX>

Technical Specifications

Brand	ABB - Thomas & Betts
Item	Cable tie
Cable Tie Type	Steel tooth
Performance	UV resistant
Material	Nylon 6.6
Series	Ty-Rap
Length	13.4in
Width	0.28in
Tensile Strength	120 lb
Maximum Bundle Diameter	4in

Color	Black
UV Resistant	Yes
Temperature Rating	-76 to +185 °F
Installation Temperature	-22 °F
Flammability	UL 94 V-2
UL Rating	UL 62275
Applicable Standards	UL 62275 (cULus), CSA C22.2 No. 62275, IEC 62275 and CE 62275
Quantity per Pack	500

Agency Approvals

UL Listed File #	E49405
CE	None
CSA File #	2884
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement