

# TY527MX Cut Sheet



ABB - Thomas & Betts Ty-Rap series steel tooth cable tie, UV resistant, nylon 6.6, 13.4in length, 0.28in width, 120 lb tensile strength, 4in maximum bundle diameter, black. Package of 50.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TY527MX>

## Technical Specifications

<b>Brand</b>	ABB - Thomas & Betts
<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	Steel tooth
<b>Performance</b>	UV resistant
<b>Material</b>	Nylon 6.6
<b>Series</b>	Ty-Rap
<b>Length</b>	13.4in
<b>Width</b>	0.28in
<b>Tensile Strength</b>	120 lb
<b>Maximum Bundle Diameter</b>	4in

<b>Color</b>	Black
<b>UV Resistant</b>	Yes
<b>Temperature Rating</b>	-76 to +185 °F
<b>Installation Temperature</b>	-22 °F
<b>Flammability</b>	UL 94 V-2
<b>UL Rating</b>	UL 62275
<b>Applicable Standards</b>	UL 62275 (cULus), CSA C22.2 No. 62275, IEC 62275 and CE 62275
<b>Quantity per Pack</b>	50

## Agency Approvals

<b>UL Listed File #</b>	E49405
<b>CE</b>	None
<b>CSA File #</b>	2884
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>