

# UB14-SS Cut Sheet



NITRA pneumatic push-to-connect fitting, bulkhead union, 316 stainless steel body, (1) 1/4in push-to-connect to (1) 1/4in push-to-connect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UB14-SS>

## Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Type	Bulkhead union
Body Material	316 stainless steel
Thread Sealant	No
Fitting Measurement Type	SAE
Connection	(1) 1/4in push-to-connect to (1) 1/4in push-to-connect
Operating Pressure	-29.5in Hg to 290 psi
Operating Temperature	32 to 390 deg F
For Use With	Flexible pneumatic tubing

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/UB14-SS.pdf>  
See store item page for other formats.