

UG01-0001-40 Cut Sheet



Flowline EchoPod reflective ultrasonic liquid level sensor, 4.9ft (1.5m) sensing range, 4-20 mA or (4) SPST relays, N.O./N.C. selectable, 14-28 VDC operating voltage, 2in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UG01-0001-40>

Technical Specifications

Brand	Flowline
Series	EchoPod
Item	Level sensor
Sensor Type	Reflective ultrasonic
Media Type	Liquid
Sensing Range	4.9ft (1.5m)
Output	4-20 mA and (4) SPST relays, N.O./N.C. selectable
Operating Voltage	14-28 VDC
Housing Rating	NEMA 6P (IP68)
Process Connection	2in male NPT
Electrical Connection	48in integral 9-conductor shielded cable
Requires	An LI99-2001 Fob USB adapter (purchased separately) and WEBCAL software (free download from the AutomationDirect Web site) are required for sensor configuration and firmware updates

Agency Approvals

CE	View CE declarations
CSA File #	178551
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document