

# UH5947-04-001PC110 Cut Sheet



Dold safety relay, motor standstill, speed and safety gate monitoring, multi delay functions, (2) NAMUR sensor inputs and/or (1) encoder, 2-channel, 110-240 VAC/VDC, (4) N.O. safety output(s), (2) status monitoring output(s), push-in cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UH5947-04-001PC110>

## Technical Specifications

<b>Brand</b>	Dold
<b>Item</b>	Safety relay
<b>Relay Type</b>	Motor standstill, speed and safety gate monitoring
<b>Delay Type</b>	Multi delay functions
<b>Monitoring Circuit</b>	(2) NAMUR sensor inputs and/or (1) encoder
<b>Number Of Channels</b>	2
<b>Control Voltage</b>	110-240 VAC/VDC
<b>Restart Type</b>	Manual or automatic restart
<b>Safety Output Type</b>	(4) N.O.
<b>Monitoring Output Type</b>	(2) status
<b>Connection</b>	Push-in cage clamp

## Agency Approvals

<b>UL Listed File #</b>	E107778
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/UH5947-04-001PC110.pdf>  
See store item page for other formats.