

# UK1D-GN-0E Cut Sheet



Micro Detectors ultrasonic proximity sensor, tubular, 18mm diameter x 91.6mm body, polybutylene terephthalate housing, NPN, N.O./N.C. selectable output, 150-1600mm sensing distance, 3 Hz switching frequency, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UK1D-GN-0E>

## Technical Specifications

Brand	Micro Detectors
Item	Proximity sensor
Sensor Type	Ultrasonic
Shape	Tubular
Housing Size	18mm diameter x 91.6mm body
Housing Material	Polybutylene terephthalate
Barrel Type	Threaded
Sensing Method	Diffuse
Adjustable	Yes
Number of Wires	4

Switching Output	NPN
Operation Mode	N.O./N.C. selectable output
Sensing Distance	150-1600mm
IO-Link Compatible	No
Switching Frequency	3 Hz
Operating Voltage	10-30 VDC
IP Rating	IP67
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware

## Agency Approvals

UL Listed File #	E187310
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/UK1D-GN-0E.pdf>  
See store item page for other formats.