

# UL10M-SS Cut Sheet



NITRA pneumatic push-to-connect fitting, union elbow, 316 stainless steel body, (1) 10mm push-to-connect to (1) 10mm push-to-connect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UL10M-SS>

## Technical Specifications

|                                 |   |
|---------------------------------|---|
| <b>Brand</b>                    | NITRA   |
| <b>Item</b>                     | Fitting   |
| <b>Working Fluid</b>            | Air or inert gas  |
| <b>Fitting Connection Type</b>  | Push-to-connect   |
| <b>Fitting Type</b>             | Union elbow   |
| <b>Body Material</b>            | 316 stainless steel                                     |
| <b>Thread Sealant</b>           | No  |
| <b>Fitting Measurement Type</b> | Metric  |
| <b>Connection</b>               | (1) 10mm push-to-connect to<br>(1) 10mm push-to-connect |
| <b>Operating Pressure</b>       | -29.5in Hg to 290 psi                                   |
| <b>Operating Temperature</b>    | 32 to 390 deg F   |
| <b>For Use With</b>             | Flexible pneumatic tubing                               |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/UL10M-SS.pdf>  
See store item page for other formats.