

UL16M Cut Sheet



NITRA pneumatic push-to-connect fitting, union elbow, thermoplastic (PBT) body, (2) 16mm tube connection(s). Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UL16M>

Technical Specifications

Brand	NITRA
Item	Pneumatic Push-to-connect Fitting
Fitting Type	Union elbow
Body Material	Thermoplastic (PBT)
Thread Sealant	No
Connection	(2) 16mm push-to-connect
Operating Pressure	-29.5in Hg to 150 psi
Operating Temperature	32 to 140 deg F
Quantity per Pack	5
For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document