

UL516-P Cut Sheet



HydroMode potable water push-to-connect fitting, union elbow, acetal body, (2) 5/16in tube connection(s), NSF/ANSI 61. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UL516-P>

Technical Specifications

| | |
|------------------------------|---------------------------------------|
| Brand | HydroMode |
| Item | Potable water Push-to-connect Fitting |
| Fitting Type | Union elbow |
| Body Material | Acetal |
| Port Connection Info | (2) 5/16in tube |
| Operating Pressure | 145 psi |
| Operating Temperature | 32 to 158 deg F |
| Agency Approval | NSF/ANSI 61 |
| Quantity per Pack | 5 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |