

# UL532-P Cut Sheet



HydroMode potable water push-to-connect fitting, union elbow, acetal body, (2) 5/32in tube connection(s), NSF/ANSI 61. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UL532-P>

## Technical Specifications

Brand	HydroMode
Item	Fitting
Working Fluid	Potable water
Fitting Connection Type	Push-to-connect
Fitting Type	Union elbow
Body Material	Acetal
Connection	(2) 5/32in push-to-connect
Operating Pressure	145 psi
Operating Temperature	32 to 158 deg F
Potable Water Certifications	NSF/ANSI 61
Quantity per Pack	5

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/UL532-P.pdf>  
See store item page for other formats.