

ULPCM10060T Cut Sheet



Fibox MNX series enclosure, NEMA 1/4/4X/6, 130 x 80 x 60 mm (HxWxD), polycarbonate, RAL 7035 light gray, smoke screw cover, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ULPCM10060T>

Technical Specifications

Brand	Fibox	Enclosure Width	80.00 mm
Item	Enclosure	Enclosure Depth	61.00 mm
Series	MNX	Cover Type	Smoke screw cover
Subpanel	Purchase subpanel separately	Cover Depth	11 mm
NEMA Rating	1/4/4X/6	Integral Mounting Flange	No
IP Rating	IP67	Material	Polycarbonate
Enclosure Height	130.00 mm	Color	RAL 7035 light gray

Agency Approvals

UL Listed File #	E75645
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ULPCM10060T.pdf>
See store item page for other formats.