

ULPCM175150XG Cut Sheet



Fibox MNX series enclosure, NEMA 1/4/4X/6, 180 x 180 x 150 mm (HxWxD), polycarbonate, RAL 7035 light gray, screw cover, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ULPCM175150XG>

Technical Specifications

Brand	Fibox
Item	Enclosure
Series	MNX
Subpanel	Purchase subpanel separately
NEMA Rating	1/4/4X/6
IP Rating	IP67
Enclosure Height	180.00 mm

Enclosure Width	180.00 mm
Enclosure Depth	151.00 mm
Cover Type	Screw cover
Cover Depth	77 mm
Integral Mounting Flange	No
Material	Polycarbonate
Color	RAL 7035 light gray

Agency Approvals

UL Listed File #	E75645
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ULPCM175150XG.pdf>
See store item page for other formats.