

ULPCM200125XG Cut Sheet



Fibox MNX series enclosure, NEMA 1/4/4X/6, 255 x 180 x 125 mm (HxWxD), polycarbonate, RAL 7035 light gray, screw cover, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ULPCM200125XG>

Technical Specifications

Brand	Fibox	Enclosure Width	180.00 mm
Item	Enclosure	Enclosure Depth	127.00 mm
Series	MNX	Cover Type	Screw cover
Subpanel	Purchase subpanel separately	Cover Depth	52 mm
NEMA Rating	1/4/4X/6	Integral Mounting Flange	No
IP Rating	IP67	Material	Polycarbonate
Enclosure Height	255.00 mm	Color	RAL 7035 light gray

Agency Approvals

UL Listed File #	E75645
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ULPCM200125XG.pdf>
See store item page for other formats.