UPR-A500-120DSH Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



RHINO AC uninterruptible power supply, standby, 120 VAC 50/60Hz @ 7.08A/850VA, 120 VAC 50/60 Hz nominal input, 1-phase, enclosed, metal housing.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/UPR-A500-120DSH

Technical Specifications

Brand	RHINO AC
Item	Uninterruptible power supply
Power Supply Type	Standby
Output Configuration	Single output
Output	120 VAC 50/60Hz @ 7.08A/850VA
Output Voltage Range	114–126 VAC
Input voltage range	96–132 VAC
Number of Input Phases	1
Protection Type(s)	Short circuit and overload protection
Remote On/Off	Yes
Enclosure Type	Enclosed

Housing Material	Metal
IP Rating	IP20
Mounting	35mm DIN rail
Connector Type	Screw terminals
Operating Temperature	0–49 °C
Backup Time	2 min @ 100% load
Indicating Type	(1) status LED and audible alarm
Includes	Auxiliary DC output and integral data surge protection
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	YEDU2.E550237,YEDU8.E550237
UL Hazardous File #	YEEU2.E550236,YEEU8.E550236
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/UPR-A500-120DSH.pdf
See store item page for other formats.