

# UR38-516-B Cut Sheet



NITRA pneumatic push-to-connect fitting, union straight reducer, nickel-plated brass body, (1) 3/8in push-to-connect to (1) 5/16in (8mm) push-to-connect. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UR38-516-B>

## Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Type	Union straight reducer
Body Material	Nickel-plated brass
Fitting Measurement Type	Metric and SAE
Connection	(1) 3/8in push-to-connect and (1) 5/16in (8mm) push-to-connect
Operating Pressure	0 to 300 psi
Operating Temperature	0 to 175 deg F
Quantity per Pack	5
For Use With	Flexible pneumatic tubing

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/UR38-516-B.pdf>  
See store item page for other formats.