

UR38-516 Cut Sheet



NITRA pneumatic push-to-connect fitting, union straight reducer, thermoplastic (PBT) body, 3/8in tube to 5/16in (8mm) tube connection(s). Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UR38-516>

Technical Specifications

Brand	NITRA
Item	Pneumatic Push-to-connect Fitting
Fitting Type	Union straight reducer
Body Material	Thermoplastic (PBT)
Thread Sealant	No
Connection	3/8in push-to-connect and 5/16in (8mm) push-to-connect
Operating Pressure	-29.5in Hg to 150 psi
Operating Temperature	32 to 140 deg F
Quantity per Pack	5
For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document