UR8M-6M-B Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

NITRA pneumatic push-to-connect fitting, union straight reducer, nickel-plated brass body, (1) 5/16in (8mm) push-to-connect to (1) 6mm push-to-connect. Package of 5.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/UR8M-6M-B

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Type	Union straight reducer
Body Material	Nickel-plated brass
Thread Sealant	No

Fitting Measurement Type	Metric and SAE
Connection	(1) 5/16in (8mm) push-to-connect and (1) 6mm push-to-connect
Operating Pressure	0–300 psi
Operating Temperature	0–175 °F
Quantity per Pack	5
For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/UR8M-6M-B.pdf
See store item page for other formats.