

# UR8M-6M-SS Cut Sheet



NITRA pneumatic push-to-connect fitting, union straight reducer, 316 stainless steel body, 5/16in (8mm) tube to 6mm tube connection(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UR8M-6M-SS>

## Technical Specifications

|                              |  |
|------------------------------|--|
| <b>Brand</b>                 | NITRA  |
| <b>Item</b>                  | Pneumatic Push-to-connect Fitting                    |
| <b>Fitting Type</b>          | Union straight reducer                               |
| <b>Body Material</b>         | 316 stainless steel                                  |
| <b>Thread Sealant</b>        | No   |
| <b>Connection</b>            | 5/16in (8mm) push-to-connect and 6mm push-to-connect |
| <b>Operating Pressure</b>    | -29.5in Hg to 290 psi                                |
| <b>Operating Temperature</b> | 32 to 390 deg F                                      |
| <b>For Use With</b>          | Flexible pneumatic tubing                            |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |