

URMPV37 Cut Sheet



WEG Electric field installable undervoltage trip, right side mount, 230-240 VAC (50Hz)/240-277 VAC (60Hz) sensing range, screw terminals. For use with MPW40 and MPW80 series manual motor protectors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/URMPV37>

Technical Specifications

Brand	WEG Electric
Item	Undervoltage trip
Field Installable	Yes
Mounting	Right side
Sensing Range	230-240 VAC (50Hz)/240-277 VAC (60Hz)
Connection	Screw terminals
For Use With	MPW40 and MPW80 series manual motor protectors
Additional Information	May not be used together with a shunt trip device

Agency Approvals

UL Listed File #	E172121
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/URMPV37.pdf>
See store item page for other formats.