

US-UW-30 Cut Sheet



di-soric right-angle beam adapter, polyoxymethylene (POM), 30mm. For use with di-soric 30mm ultrasonic sensors. Allows 90 degree sound deflection, threads on to head of sensor.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/US-UW-30>

Technical Specifications

| | |
|-------------------------------|---|
| Brand | di-soric |
| Item | Right-angle beam adapter |
| Material | Polyoxymethylene (POM) |
| Size | 30mm |
| For Use With | Di-soric 30mm ultrasonic sensors |
| Additional Information | Allows 90-degree sound deflection, threads on to head of sensor |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/US-UW-30.pdf>
See store item page for other formats.