

# US14-B Cut Sheet



NITRA pneumatic push-to-connect fitting, union straight, nickel-plated brass body, (2) 1/4in push-to-connect. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/US14-B>

## Technical Specifications

|                                |                           |
|--------------------------------|---------------------------|
| <b>Brand</b>                   | NITRA                     |
| <b>Item</b>                    | Fitting                   |
| <b>Working Fluid</b>           | Air or inert gas          |
| <b>Fitting Connection Type</b> | Push-to-connect           |
| <b>Fitting Type</b>            | Union straight            |
| <b>Body Material</b>           | Nickel-plated brass       |
| <b>Connection</b>              | (2) 1/4in push-to-connect |
| <b>Operating Pressure</b>      | 0 to 300 psi              |
| <b>Operating Temperature</b>   | 0 to 175 deg F            |
| <b>Quantity per Pack</b>       | 5                         |
| <b>For Use With</b>            | Flexible pneumatic tubing |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/US14-B.pdf>  
See store item page for other formats.